



● Block diagram




● Dimensional diagram



Main unit : W750xD1250xH1930 mm

SPS Series


SPS2000 Spark Plasma Sintering System



Patent No. 7578259
Patent No. 7602302


Received MEXT Minister's Award
- Spark Plasma Sintering system with
DEGAS Function -

○ Issue to be solved.



The pressure in "P1" increases due to outgassing from the powder surface which is released by heating during sintering. Even in the high vacuum condition, the conductance of the evacuation path of "P1" is extremely small, so the impurities adhering to the powder could not be fully removed.

○ Suga's "DEGAS MODE" offers solution!



SPS2000 can preheat the powder in the vacuum chamber before the sintering process and release the upper surface of the powder into vacuum condition so that outgassing from the powder can be efficiently evacuated.

SUGA Co., Ltd.

Head office: 3-2-2, Oiwake, Hokuto-shi, Hokkaido, 049-0101, Japan
Branch offices: Tokyo, Sapporo, Shizuoka

TEL. +81-50-3734-0730

URL : <https://www.agus.co.jp/en>



* Product specifications are subject to change without notice.
* Notice of Export Control : In the event that any product described or contained herein falls under the category of strategic products controlled by the Foreign Exchange and Foreign Trade Control Law of Japan, exporting of such products shall require an export license from the Japanese government in accordance with the above law.

SPS2000 is the only SPS system that incorporates the DEGAS mode (powder cleaning step). It is a compact and lightweight SPS system with stylish design that guarantees not only high operability and safety but the new functions required for advanced material development. Additional options are available even after the installation. Pressurization capacity and DC pulse generator can be added up to the maximum specifications at affordable cost and simple procedures. In addition, SUGA's ALD and Sputtering systems for the deposition on powders could be a unique innovative solution.

● Features


■ Selectable pre/after sintering process mode

In addition to the regular sintering control, the following modes can be selected and automatically controlled in a series of operations.

Pre-sintering

w/o heat


A mechanism that efficiently evacuates the atmosphere from the boundary of powder particles to maintain better purity on the material.



Pre-sintering

w/ heat


A mechanism that heats powder in a vacuum atmosphere to remove water molecules, etc. on the powder surface for better purity of sintered compacts.




After-sintering

Rapid cooling mode

Rapid cooling mechanism that blows cooling gas onto the die after sintering






[Reference] φ10mm punch
Natural cooling 800 °C → 80 °C : Approx. 29 min
Rapid cooling 800 °C → 80 °C : Approx. 11 min

■ Selectable Wave Form

Continuous DC and Full Wave can be selected on a touch screen in addition to DC Pulse (Standard output for SPS)



■ FLASH SPS

Densification within a few seconds.
Heating rate: 10²-10³ C/min.

Signal tower for easy monitoring

Space saving/light weight

Selectable wave forms

Thorough management of cooling function

Upgrade for DC output and pressurization are available

DP/TMP as an option for high vacuum *

Easy operability


Professional Data logger and PC *
Mounting arm can be set either on the right or left side of the machine

User friendly spacious chamber for easy handling and cleaning

Transferable with casters

* : Option

AUTO control flow chart



● Specification

Specifications				
Model		SPS2000-3T	SPS2000-5T	SPS2000-7T
Max. pressure		30kN	50kN	70kN
Min. pressure		0.2kN (20kgf)		
SPS current		1000A	2000A	3000A
Stroke		150mm (open height : 200mm)		
Max. temperature		2500℃ (working temp. 2200℃)		
Pressurization system		AC Servo motor		
DC pulse control		ON/1～999ms OFF/1～99ms		
Vacuum chamber		Rectangular-shaped water cooled system		
Vacuum speed		2Pa / 5 min		
Weight	Main unit	600kg	725kg	850kg
	RP pump	27kg		

Option		
High vacuum	DP (Diffusion Pump)	≦ 5×10 ⁻⁴ Pa
	TMP(Turbo molecular pump)	
Radiation thermometer	for above 600℃	
PC for data logger	Windows notebook with mounting arm	
Chiller	for cooling water	

Max. output of DC pulse generator can be increased in increments of 500A as an option up to 3000A.

Utility							
Model		SPS2000-3T	SPS2000-5T	SPS2000-7T	Cooling water	Water amount	≥10L/min
SPS current (standard)		1000A	2000A	3000A		Supply pressure	0.2~0.3MPa (back pressure ≤0.05MPa)
Rated input	Power supply	3 φ 200/380/400/480V±10% 50/60Hz				Temp.	15~30℃
		18.2kVA	32.2kVA	46.2kVA			
	Input cable	Length: 5m (User's side is unconnected)			Port	Rc3/8	
Exhaust duct	Port	NW25(KF25) Flange			Compressed air	Supply pressure	0.5~0.8MPa
Required space (inclusive of maintenance space)		W1300xD1600xH2500 mm				Port	Rc1/8